

---

## PUNCTOLED IP65

### LED downlights



---

#### Product benefits

- Pleasant homogenous light
- Long lifetime thanks to LED technology
- Low profile

---

#### Product features

- Recessed LED downlight
- Type of protection: IP65
- Extremely low profile
- Solid aluminum housing in white
- Beam angle: 90°
- Color temperature: 3,000 K
- Lifetime: up to 50,000 h
- Protection class: II
- Dimmable (with suitable Phase-cut dimmers)



# Product family datasheet

## Technical data

Product description	Electrical data			Photometrical data				Light technical data
	Operating mode	Nominal wattage	Nominal voltage	Color temperature	Luminous flux	Light color as per EN 12464-1	Color rendering index Ra	Beam angle
PUNCTOLED IP65 10 W WT	ECG	10 W	220...240 V	3000 K	600 lm	Warm white	≥ 80	90 °
PUNCTOLED IP65 2X5.5 W WT	ECG	5.5 W	220...240 V	3000 K	330 lm	Warm white	≥ 80	90 °

  

Product description	Dimensions & weight		Colors & materials		Capabilities		Certificates & standards	
	Diameter	Height	Body material	Product color	Type of installation	Adjustable	Protection class	Type of protection
PUNCTOLED IP65 10 W WT	110.0 mm	43.0 mm	Aluminum	White	Recessed	No	II	IP65
PUNCTOLED IP65 2X5.5 W WT	80.0 mm	35.0 mm	Aluminum	White	Recessed	No	III	IP65

  

Product description	Country specific categorizations
	Order reference
PUNCTOLED IP65 10 W WT	41194
PUNCTOLED IP65 2X5.5 W WT	41193

## Product family datasheet

---

### Equipment / Accessories

- External control gear included (cabled on the secondary side)

---

### Application advice

For more detailed application information and graphics please see product datasheet.

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.