



**Part Number :** [5051105596](#)  
**Product Description :** Easy-On FFC/FPC Connector, 0.50mm Pitch, FD19 Series, Right-Angle, Bottom Contact, 1.90mm Height, 55 Circuits, 150°C Operating Temperature, Gold over Nickel Plating  
**Series Number :** 505110  
**Status :** Active  
**Product Category :** FFC / FPC Connectors



Documents & Resources

**Drawings**  
[5051105596\\_sd.pdf](#)

**3D Models and Design Files**  
[5051105596\\_stp.zip](#)

**Specifications**  
[5051109200-200.pdf](#)  
[5051100008-PS-000.pdf](#)

Product Environment Compliance

Compliance

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                          |
| China RoHS         |  |
| EU ELV             | Not Relevant                                                                          |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                        |
| REACH SVHC         | Not Contained per D(2024)6225-DC (07 Nov 2024)                                        |
| EU RoHS            | Compliant per EU 2015/863                                                             |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

|              |                                                                                                                                                                      |
|--------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Status       | Active                                                                                                                                                               |
| Category     | FFC / FPC Connectors                                                                                                                                                 |
| Series       | 505110                                                                                                                                                               |
| Description  | Easy-On FFC/FPC Connector, 0.50mm Pitch, FD19 Series, Right-Angle, Bottom Contact, 1.90mm Height, 55 Circuits, 150°C Operating Temperature, Gold over Nickel Plating |
| Series Name  | FD19                                                                                                                                                                 |
| Comments     | Black Actuator                                                                                                                                                       |
| Product Name | Easy-On                                                                                                                                                              |
| UPC          | 191128824521                                                                                                                                                         |

#### Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 0.5A |
| Voltage - Maximum             | 50V  |

#### Physical

|                                |              |
|--------------------------------|--------------|
| Actuator Type                  | Front Flip   |
| Circuits (Loaded)              | 55           |
| Circuits (maximum)             | 55           |
| Color - Resin                  | Beige        |
| Contact Position               | Bottom       |
| Durability (mating cycles max) | 20           |
| Mated Height                   | 1.90mm       |
| Material - Metal               | Copper Alloy |
| Material - Plating Mating      | Gold         |
| Material - Plating Termination | Gold         |

|                               |                        |
|-------------------------------|------------------------|
| Material - Resin              | Liquid Crystal Polymer |
| Net Weight                    | 404.100/mg             |
| Orientation                   | Right Angle            |
| Packaging Type                | Embossed Tape on Reel  |
| PCB Locator                   | No                     |
| PCB Mounting                  | Surface Mount          |
| PCB Retention                 | Yes                    |
| Pitch - Mating Interface      | 0.50mm                 |
| Pitch - Termination Interface | 0.50mm                 |
| Plating min - Mating          | 0.051µm                |
| Plating min - Termination     | 0.051µm                |
| Polarized to PCB              | Yes                    |
| Stackable                     | No                     |
| Temperature Range - Operating | -40° to +150°C         |
| Wire/Cable Type               | FFC/FPC                |