



Sample photo

Order symbol: P 081906
Product nbr: 7094190
Description: Enclosure
Remarks: Polyester

EAN: 6418074004369
EI. number:
 Finland 3423658
 Denmark 8212005633
 Italy 7331025
 Sweden 2536211

Including: Base, cover with EPDM gasket and stainless steel cover screws.

Dimensions:	L	W	H
mm:	75	190	55
inch:	3	7.5	2.2

Materials:	
Material:	GRP
Base colour:	RAL 7001
Cover colour:	RAL 7001
Cover screws material:	Stainless steel
Gasket material:	EPDM

Temperatures:	
Short term:	-50 ... 120 °C
Continuous:	-40 ... 80 °C
Short term:	-60 ... 250 °F
Continuous:	-40 ... 175 °F

Accessories:	
PM 0819	Mounting plate
PRM 0819	DIN-15 Mounting rail
MRS 28540	Wall fastening lug set

Rating:
Ingress Protection (EN 60529): IP 66/67
Impact Resistance (EN 50102): IK 08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
UV resistance: UL 508
Flammability Rating (UL 746 C 5): UL 94 5V
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 4, 4X, 12, 13

Certificates:

