

## FEATURES

- PVC sheath material for insulation
- H07V-K Standard
- Sizes range from 1.5mm<sup>2</sup> CSA/15 AWG up to 10mm<sup>2</sup> CSA/7 AWG
- Supplied on a 100m reel

## RS PRO Green/Yellow, 6 mm<sup>2</sup> Hook Up Wire, 100m

RS Stock No.: 535-997



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Brought to you by RS PRO, a range of hook up wire. Suitable for electrical power, lighting and internal wiring applications. All of the standard equipment wire within this range is 100 m in length and with a variety of sheath colours to choose from, they are suitable for various applications. Due to robust and carefully manufactured copper conductor, all models are highly reliable and excellent quality.

## General Specifications

Type	Hook-up wire
Conductor Material	Bare Copper
Sheath Colour	Yellow/Green
Insulation Material	PVC
Wire Style	2491X
Application	Circuit boards, Computer Internals, Vehicle lights, Mobile phones and other battery operated devices

## Electrical Specifications

American Wire Gauge	9AWG
Voltage Rating	450/750V
Current Rating	41A
Harmonised Code	H07V-K

## Mechanical Specifications

Cross Sectional Area	0.6mm <sup>2</sup>
Outer Diameter	4.7mm
Length	100m

## Operation Environment Specifications

Minimum Operating Temperature	5°C
Maximum Operating Temperature	70°C
Operating Temperature Range	5°C to 70°C

## Approvals

Standards Met	Harmonised Certified; RoHS Compliant
---------------	--------------------------------------

