

Features

- 5 mm pitch
- Voltage Rating: 300V
- Current Rating: 15A
- Low Mating Force
- 2 WAY CLAMP PCB SCREW TERMINAL

RS PRO 5MM PITCH 2 WAY CLAMP 15A PCB SCREW TERMINAL

RS Stock No.: 0631114



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- Vertical cable mount terminal block plug connectors with a 5.0mm pitch and a 300V 15A rating. These 5.0mm cable mount pluggable terminal blocks have M3.0 rising cage clamp screw terminals that accept a wire size range of 28 to 12 AWG and green PA66 housings
- Standard accepts wire 28-12AWG 2.5 mm²

General Specifications

Number of Contacts	2
Number of Rows	1
Pitch	5mm
Mounting Type	Through Hole
Type	PCB Terminal Block
Body Orientation	Straight
Number of P	2
Termination Method	Screw (M3, Steel(A3), Zinc Plated
Torque	0.5N.m
Clamp	Phosphor Bronze, Nickel Plated
Wire Cage Material	Brass or Steel
Wire Cage Plating	Nickel Plated
Housing	PA66(UL94V-0)
Colour	Green

Electrical Specifications

Voltage Rating	300V
Current Rating	15A
Insulation Resistance	500M ohm min

Withstanding Voltage	2500V AC/minute
----------------------	-----------------

Mechanical Specifications

Mounting Type	Through Hole
Pitch	5.0 mm
Pin size	Please see below drawings

Operation Environment Specifications

Operating Temperature	-40°C to 105°C
-----------------------	----------------

Approvals

Compliance/Certifications	RoHS Compliant, UL, CE
Declarations	Reach

Spec Drawings

