

40132

Nylon Hand Scraper, 100 mm, Green



Suitable for loosening stubborn dirt like pastry, chocolate, burnt on food, etc. on smooth surfaces. The nylon blade is a good alternative to a stainless steel blade and can be used on sensitive surfaces to avoid scratches on equipment and sensitive conveyor belts. The hard blade can withstand hot surfaces when used at intervals of max. 2 minutes at a time.

Technical Data

Item Number	40132
Blade Thickness	2,7 mm
Material	Nylon Polypropylene
Complies with (EC) 1935/2004 on food contact materials¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates	No
Is Halal compliant	Yes
Box Quantity	10 Pcs.
Quantity Per Layer (Pallet)	150 Pcs.
Box Length	260 mm
Box Width	230 mm
Box Height	85 mm
Length/Depth	235 mm
Width	100 mm
Height	20 mm
Gross Weight	0,09 kg
Net Weight	0,076 kg
Cubik metre	0,0005 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. usage temperature (for food contact)	175 °C
Max usage temperature (non food contact)	175 °C
Min. usage temperature³	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Recycling Symbol "7", Miscellaneous Plastics	Yes
GTIN-13 Number	5705022004597
GTIN-14 Number (Box quantity)	15705028004604
Commodity Code	39241000
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

3. Do not store the product below 0° Celsius.