

RS Part Number: **466-249**
 Specifications and dimensions



- Boxed isolator 4 pole
- ABS plastic enclosure with padlockable handle

Specifications	
Height	125 mm
Width	100 mm
Depth	74 mm
Depth including switch	118 mm
Degree of protection	IP65
Rated operational current Ie AC21A	20 A
Rated operational current Ie AC22A	16 A
Rated operational voltage Ue IEC & EN	690 V
Rated operational power AC23A 380-440V	11 kW
Rated operational power AC3 440V	5.5 kW
Maximum gL fuse size IEC	20 A
Rated fused short circuit capacity IEC	5 kA
Knockout size	20 mm
Normal operating temperature	-25°C to +40°C
Maximum cable capacity	6 mm ²
Recommended tightening torque	1.7 Nm
Number of possible auxilliary contacts	None