



Product data sheet

Power tools for trade & industry

Angle Grinder

PRO GWS18V-11PS



Revolutionizing Comfort with Ergonomic Design for Ultimate Control

The most important data

Battery voltage	18.0 V
No-load speed	3,000 – 9,000 rpm
Disc diameter	125 mm

Part Number 0 601 9N4 300

Technical data

Technical data

Disc diameter	125 mm
Packaging dimensions (width x length x height)	135 x 390 x 160 mm
X-LOCK	No
BITURBO	No
No-load speed	3,000 – 9,000 rpm
Battery voltage	18.0 V
Grinding spindle thread	M14
Bore size, diameter	22.23 mm
Weight excl. battery	1.9 kg

Noise/vibration information

Surface grinding (roughing)

Vibration emission value ah	5.2 m/s ²
Uncertainty K	1.5 m/s ²

Sanding with sanding sheet

Vibration emission value ah	2 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Superior ergonomics for comfortable cutting and grinding with a rotatable handle
- All-round protection features with kickback, an intelligent brake system and paddle switch
- High-performance with the equivalent of 1,100W corded power
- Ergonomic and easy to use thanks to long, slim hand grip
- Eases fatigue with comfortable anti-vibration handle



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

