

Datasheet

RS Pro 57 mm Hardal SUPRA (HDS) End Mill, 13mm Cut Length, 6mm Cut Diameter, 4 Flutes

RS Stock No: **736-9508**



Product Details

RS Pro 57 mm hardal SUPRA (HDS) end mill offers a new high performance alternative to conventional HSS and carbide endmill. This high speed alloy with a hardness of up to 70HRC guarantees an extremely stable cutting edge. The TiALN Black Panther coating gives the necessary resistance to heat and oxidation. This combination allows the HDS endmill to show excellent results even when run dry. It has 13 mm cut length and 6 mm cut diameter with 4 flutes.

Features and Benefits

- High tensile strength
- Very good wear resistance
- Suitable for dry cutting
- Extreme oxidation resistance
- Black Panther coating DN 630+



ENGLISH

Specifications:

Cut Length	13 mm
Cutter Diameter	6 mm
Material	Hardal SUPRA (HDS)
Number of Flutes	4
Overall Length	57 mm
Shank Diameter	6 mm
Shank Type	Weldon