



# FLEXIBLE WHIP ANTENNA

## RRST-VA4-16512-30-A-001

### ■ SPECIFICATION

	VALUE
Frequency Range	433 MHz
Bandwidth	±3 MHz
Input Impedance	50 Ω
VSWR, max	1.5
Polarization	Vertical
Radiation	Omni-directional
Gain	2.5 dBi
Power, max	50 W
Connector	M4
Dimensions	16 x Φ12 mm
Weight	13 g
Operating Temperature Range	-40 ~ +70°C



### ■ APPROVAL

RS PRO	
DRAWN BY:	AR, June 1, 2018
APPROVED BY:	CP, June 1, 2018
REVISION:	A, Initial Release