



Armstrong Black Oxidized C Hook Wrench with 2 → 4 3/4in Jaw Capacity

Features

- Incorporates One Adjustable Hook which is designed to Adjust Threaded Collars, Locknuts, Rings, Packing Nuts, in Industrial Applications.
- Manufactured From High Alloy Steel Using the Most Up-To-Date Manufacturing Process and Heat Treat for Greater Strength and Durability

Specification

Finish	Black Oxidized
Maximum Jaw Capacity	4 3/8in
Minimum Jaw Capacity	2in
Overall Length	11 3/8 in