


pressure transmitter SPTE-V1R-Q4-B-2.5K

Part number: 571472

FESTO



Data sheet

| Feature | Value |
|---|--|
| Authorisation | RCM Mark c UL us - Recognized (OL) |
| CE mark (see declaration of conformity) | to EU directive for EMC |
| Materials note | Conforms to RoHS |
| Measured variable | Relative pressure |
| Measurement method | Piezoresistive pressure sensor |
| Pressure measuring range, initial value | 0 bar |
| Pressure measuring range, final value | -1 bar |
| Overload range | 5 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible |
| Medium temperature | 0 ... 50 °C |
| Ambient temperature | 0 ... 50 °C |
| Accuracy, FS | 3 %FS |
| Repetition accuracy in ± %FS | 0.3 %FS |
| Temperature co-efficient in ± %FS/K | 0.05 %FS/K |
| Analogue output | 1 - 5 V |
| Rise time | 1 ms |
| Min. load resistance, voltage output | 15 kOhm |
| Short circuit strength | for all electrical connections |
| Operating voltage range DC | 10 ... 30 V |
| Polarity protected | for all electrical connections |
| Electrical connection | Cable Open end 3-core |
| Cable length | 2.5 m |
| Mounting type | with accessories |
| Assembly position | Any |
| Pneumatic connection | QS-4 |
| Product weight | 35 g |
| Material housing | PA-reinforced |
| Protection class | IP40 |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |