



3 YEARS
MANUFACTURER
GUARANTEE



Product number 9171401901
EAN 3281854019012

TECHNICAL DATA

Cable quality	Rubber-Neoprene
Product number	9171401901
Luminous flux	12600 lm
Power consumption	96.5 W
Luminous efficacy	125 lm/W
Energy efficiency class	A E
Colour temperature	6500 K
Colour rendering index	80-89 (class 1B)
Nominal input voltage	230 V

Min.-Max. Nominal input voltage	220 V - 240 V
Lifetime	30000 h
Cable length	5 m
Cable designation	H07RN-F 3G1,5
With socket outlet	true
Number of socket outlets	1
Impact strength	IK08
Protection class	I
Degree of protection (IP)	IP54
Colour	black

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1
Weight of product (without packaging)	4.4 kg
Dimension LxWxH (without packing)	28 cm x 28 cm x 34.5 cm

Weight of product (including packaging)	5.02 kg
Dimension LxWxH (incl. packing)	29 cm x 29 cm x 35.5 cm