



# 313.6343

## CONNECTOR

63A 2P+E 6h 200-250V 50Hz 60Hz Mantle terminals

Product Approvals

TECHDATA		STANDARDS AND LAWS	
Commercial series	OPTIMA Series	EN 60309-1 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Type of product	CONNECTOR	EN 60309-2 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Synthetical description	CONNECTOR		
Mounting version	PORTABLE		
Rated current	63A	EN 60309-1/A1 (2007)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Poles	2P+E	EN 60309-2/A1 (2007)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Hour position	6h		
Rated voltage (range)	200-250V	EN 60309-1/A2 (2012)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Rated voltage	200-250V		
Working frequency	60Hz	EN 60309-2/A2 (2012)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Working frequency	50Hz		
Colour	BLUE	DIRECTIVE LOW VOLTAGE 2014/35 /UE	[European Directives] Low Voltage Directive
Material	THERMOPLASTIC		
Protection degree	Splash proof		
Protection degree IP	IP44/IP54		
Types of available outlets	STRAIGHT		
Terminals	Mantle terminals		
Cable outlet	CABLE GLAND		