

2 Port USB VGA Cable KVM Switch - USB Powered with Remote Switch

Product ID: SV211USB



The SV211USB 2-Port VGA Cable KVM Switch lets you control two VGA, USB-equipped PCs with a single monitor, keyboard and mouse.

To help organize your desk without sacrificing valuable work space, this VGA USB KVM switch features a compact footprint and integrated KVM cables that can be connected directly to your systems. Plus, the KVM is USB-powered, eliminating the need for a bulky external power adapter and wall outlet.

This VGA KVM switch offers support for resolutions up to 2048x1536, for the ability to drive a high-resolution VGA display. For simple switching between connected systems, the KVM features a convenient push-button remote switch on a 1.5 meter (5ft) cable, as well as keyboard hot-key support and PC or Mac compatible switching software.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Great for PC test/burn-in computer control, saving the desk space required for two monitors, keyboards and mice

- Perfect for sharing computers and attached peripherals in the home or home office
- Dual system control for single user workstations, increasing user productivity in the office

Features

- Supports resolutions up to 2048x1536
- Switch PCs via push-button, hot-keys or switching software (included)
- Space-saving design, minimal footprint
- Integrated KVM cables and remote switch
- Switching software supports PC and Mac platforms
- USB Powered - No external power adapter required
- Supports hot-plugging
- Remote switch on 1.5m (5ft.) cable

Hardware

Warranty	2 Years
Audio	No
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

Performance

On-Screen Display	No
IP Control	No
Hot-Key Selection	Yes

	Port Selection Support	Push Button, Hotkeys, and Software
Connector(s)	Console Interface(s)	1 - VGA (15 pin, High Density D-Sub)
		2 - USB 2.0 Type-A (4 pin, 480Mbps)
	Host Connectors	1 - VGA (15 pin, High Density D-Sub)
		1 - USB 2.0 Type-A (4 pin, 480Mbps)
Software	OS Compatibility	Windows 2000, XP, Vista, 7, 8, 8.1, 10, 11
		Windows Server 2003, 2008 R2, 2012, 2016, 2019, 2022
		Mac OS 10.x (Tested up to 10.9), 9.x
Special Notes / Requirements	Note	OS Compatibility refers to KVM software only - the KVM itself can be used without software on any platform
Indicators	LED Indicators	1 - PC Selection indictor
Power	Power Source	USB-Powered
	Input Voltage	5V DC
	Output Voltage	5 DC
Environmental	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (4F to 140F)
	Humidity	0~90% RH Non-Condensing
Physical Characteristics	Color	Black
	Material	Plastic
	Cable Length	33.5 in [850 mm]

Product Length	3.5 in [88 mm]
Product Width	2.6 in [6.6 cm]
Product Height	0.9 in [2.3 cm]
Weight of Product	11.3 oz [321 g]

Packaging Information

Package Quantity	1
Package Length	9.8 in [24.9 cm]
Package Width	6.4 in [16.2 cm]
Package Height	2.5 in [6.4 cm]
Shipping (Package) Weight	14.2 oz [402.0 g]

What's in the Box

Included in Package	1 - KVM Switch
	1 - Software CD
	1 - Instruction Manual

****Product appearance and specifications are subject to change without notice.***