

119-4**Pin punch**

octagonal

Code **8759020** ETIM **EC002134**

EAN **4010883875905** UNSPSC **27-11-15-05**

Country of origin **Germany** eCl@ss **21-04-07-02**

Customs tariff number
82055980

**Article description**

- Acc. to DIN 6450
- GEDORE vanadium steel
- Carefully hardened and tempered along the full length
- Striking heads inductively tempered
- Working edge polished and clear varnished
- Special sizes available on request

Article information

Contents [Qty of pieces]	1	Material	Vanadium steel
Version/Execution	Carefully hardened and tempered along the full length, striking heads inductively tempered	Standard	DIN 6450
Net weight [kg]	0,061 kg	Shaft diameter	10 mm
Total length [mm]	150 mm	Octagonal shaft [mm]	10 mm
Total width [mm]	10 mm	Drift pin Ø [mm]	4 mm
Total height [mm]	10 mm	Drift pin length [mm]	50 mm