

## FEATURES

- **Non-releasable design:** Ensures a secure and permanent hold
- **380 mm length:** Accommodates larger bundles up to 105 mm in diameter
- **Tensile strength of 55 kg:** Provides robust support for heavy-duty applications
- **UV resistant:** Suitable for outdoor use, resisting degradation from sunlight
- **Wide temperature range (-40 °C to 85 °C):** Performs reliably in extreme conditions
- **Complies with RoHS and UL 94HB standards:** Meets key safety and environmental regulations

## RS PRO Non-Releasable Cable Tie, 380 mm Length

RS Stock No: 656-100



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

This RS PRO non-releasable cable tie is designed for secure bundling and organising of cables and wires. Made from durable nylon, it offers reliable performance in a variety of environments. Its UV resistance makes it suitable for outdoor use, while the black colour provides a discreet appearance.

### General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Non-Releasable
Tensile Strength	55 kg

### Protection Category

Fire Behaviour	UL 94HB
UV Resistant	Yes

### Mechanical Specifications

Length	380 mm
Material	Nylon
Maximum Bundle Diameter	105 mm
Width	7.6 mm

### Operation Environment Specifications

Maximum Operating Temperature	85 °C
Minimum Operating Temperature	-40 °C

### Approvals

Standards/Approvals	RoHS, UL94HB
---------------------	--------------