



High-pressure washer
EasyAquatak 120

The effortless cleaning solution.
Compact, quick and easy to use

[Go to product](#)



Key product features

- 120 bar cleaning power and accessories
- Compact product design that is easy to store within the home
- Quick and easy push-fit connections for faster set up

Other product advantages

- High pressure foam nozzle included as standard
- Includes a rotary nozzle for removing stubborn dirt
- Includes safe and convenient in-use gun storage feature
- Very stable in use due to low centre of gravity and broad base

Comes complete with

- Bosch high-pressure gun
- Lance
- 5 m high-pressure hose
- Fixed fan jet nozzle
- Rotary nozzle
- High pressure detergent nozzle, 450 ml
- Water filter

Part number: 06008A7970

EAN code: 3165140882699



High-pressure washer

EasyAquatak 120

Technical data

Motor power: 1.500 W

Max. pressure: 120 bar

Max. flow rate: 350 l/h

Inlet water temperature: 40 °C

Detergent system: High pressure foam

Motor type: Series

Pump type: 3 cylinder

Pump material: all metal

Cable length: 5 m

Hose length: 5 m (PVC)

Weight (without accessories): 5 kg

Nozzles: Fixed fan jet nozzle

Noise / vibration information

Measured values determined according to EN 60335
Total vibration values (vector sum of three directions).

Vibration emission value ah: 1.74 m/s²

Uncertainty K: 0.61 m/s²

Measured values for noise determined according to 2000/14/EC. The A-rated noise level of the power tool is typically as follows: Sound pressure level 80,5 dB(A); Sound power level 90,8 dB(A). Uncertainty K= 1,92 dB.

Functions



Power input

1500 watts

Functions



Compact

Ready to use out of the box

Storage for all accessories/hose/cables

Simple, quick connect fittings

Safe in-use gun storage

Self priming/use with water tanks

Water filter

All metal pump