

Enclosure

46-425.1400

Distribution by
Rs-online



<https://rs-online.eao.com/component/46-425.14...>

Your product:



46-425.1400 Enclosure

FRONT

Colour: Yellow

MOUNTING

Mounting cut-out: Ø 22.3 mm

Mounting type: Panel mounting

ELECTRICAL CHARACTERISTICS

Pollution degree: 3

Protection class: II, according to EN / IEC 61140

MECHANICAL CHARACTERISTICS

Tightening torque: 0.8 ... 1.2 Nm (7.1÷10.6 Lb-in)

Weight: 0.125 kg

AMBIENT CONDITION

IP front protection: IP66

IK front protection: IK07

Operating temperature: – 35 °C ... + 80 °C

CERTIFICATE

Approbations: CSA, UL

Conformities: CE

REACH:	REACH compliant
RoHS:	RoHS compliant
Standards:	CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

OTHER

Short Description:	Enclosure
Number of holes:	1
Dimension:	84 mm x 84 mm x 55 mm
Material:	Plastic
Product attributes:	Suitable for outdoor applications
max. number of switching elements:	2
Dimension drawings:	

