

<b>Product Name</b>	<b>FI-S20S</b>
<b>Series Name</b>	FI Series
<b>Contact spacing (mm)</b>	1.25
<b>Number of rows</b>	1
<b>Number of Contacts</b>	20
<b>Lead free</b>	-
<b>Connector type</b>	Cable side Plug housing
<b>PCB mounting type</b>	-
<b>PCB mounting method</b>	-
<b>Wire termination method</b>	Crimp
<b>Applicable wire</b>	Discrete wire
<b>Finish of contact in connecting area</b>	-
<b>Finish of contact in terminal area</b>	-
<b>Finish of contact in PCB mounting area</b>	-
<b>Material of housing</b>	Glass-filled Nylon (UL94V-0)
<b>PCB side connector styles</b>	-
<b>PCB mounted height (mm)</b>	-
<b>Electro magnetic shield function</b>	No