



AS SC-2345S246 TL26



AS SC-2345S246 TL26

E1441334

Assortment box of 285pcs, Releasable, Splicing connectors & Terminal Blocks



Product Properties:

Nominal voltage	450 V
Nominal current	32 A
Transparent	Yes
Number of clamp positions	2-6 .
With operation lever	Yes
Suitable for solid core	Yes
Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Colour	Green

Dimensions:

Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.2-4 mm²

Conductor cross section solid (solid, stranded)	0.2-4 mm²
MOQ	1 .
Unit	pcs
Nominal cross section	0.2-4 mm²
AWG-range	28-12 .
Nominal voltage	450 V

Approvals:

Approved according to CE	Yes
--------------------------	-----

Compliance:

REACH	No SVHC (Latest. 05 Nov 2025)
-------	-------------------------------

Other information:

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Splicing Connectors - Assortment Boxes
Search Description	SKV2024ERIK3 ENR2023H
Alternative SKU	ASSC-2345S246TL26
E-no	E1441334

Logistic information:

Barcode	733117641341
Country of origin	CN
E-no	E1441334
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1 .
Stock code	AS SC-2345S246 TL26
Taric code	85369010
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.