

PRODUCT-DETAILS

# TY46MD-2

## CABLE TIE 50LB 7 RED ID 1.17X1 MA



### General Information

Extended Product Type	TY46MD-2
Product ID	7TAG009510R0026
EAN	5414363064930
Catalog Description	CABLE TIE 50LB 7 RED ID 1.17X1 MA
Long Description	Identification Cable Tie - Double Strap Configuration, Red Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/215 Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 184.15mm (7.25 Inches), Width of 4.81mm (0.19 Inches), Thickness of 1.41mm (0.055 Inches), Tensile Strength Rating of 220 Newtons (50 pounds), Marking Pad Size of 30.1mm (1.185 Inches) x 26.99mm (1.062 Inches)

### Ordering

EAN	5414363064930
UPC	786210875392

### Dimensions

Product Net Width	0.19 in 4.81 mm
Product Net Depth / Length	7.25 in 184.15 mm

### Container Information

Package Level 1 Units	500 piece
Package Level 2 Units	1000 piece
Package Level 2 Width	10.5 in 267 mm
Package Level 2 Height	8.1 in 206 mm
Package Level 2 Depth / Length	12.8 in 325 mm

---

## Technical UL/CSA

---

Flammability According to UL94	V-2
-----------------------------------	-----

---



---

## Additional Information

---

Brand / Label	Ty-Rap
Color	Red
Effective Date	19680418
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES
Product Type	Identification
Tensile Strength	50 lb 220 N
Thickness	0.055 in 1.4 mm

---



---

## Certificates and Declarations (Document Number)

---

Data Sheet, Technical Information	TY46MD-2
Instructions and Manuals	TY46MD-2

---



---

## Classifications

---

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5040 >> I.D. Ties

---



---

## Categories

---

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

