

## **IS-3 Standard ; 0 ... 0.1 bar; 4...20 mA, 2-wire**

### **IS-3 Standard ; 0 ... 0.1 bar; 4...20 mA, 2-wire**

Item number: 14122676

Quantity: 1 pcs.

Order code: IS-3-0-2211-1ZZ-BALHSZZ-GTA3ZZZ-UAZZ  
6W101AIS3ZZSF2ASQOGSI3

Overview: IS-3 Standard ; 0 ... 0.1 bar; 4...20 mA, 2-wire  
@ 10 ... 30 V DC  
Accuracy: 0.5% of span  
G 1/2 B EN 837  
Sealing: without  
Wetted parts: stainless steel  
Adjustability: Zero/span adjustable  
angular connector acc. to DIN EN 175301-803 A PG9  
Cable material: without  
Cable length: without  
U+=1, U-=2  
permitted media temperature: -20...+80°C  
Approvals: ATEX/IECEX  
II 1/2G Ex ia IIC T4/T5/T6 Ga/Gb, I M1 Ex ia I Ma  
Additional certifications: without  
Special features: without  
Test protocol: without test protocol  
Additional ordering information: without  
Specifications according to data sheet: PE 81.58

Details: IS-3 Standard ; 0 ... 0.1 bar; 4...20 mA, 2-wire  
@ 10 ... 30 V DC  
Accuracy: 0.5% of span  
G 1/2 B EN 837  
Sealing: without  
Wetted parts: stainless steel  
Adjustability: Zero/span adjustable  
angular connector acc. to DIN EN 175301-803 A PG9  
Cable material: without  
Cable length: without  
U+=1, U-=2  
permitted media temperature: -20...+80°C  
Approvals: ATEX/IECEX  
II 1/2G Ex ia IIC T4/T5/T6 Ga/Gb, I M1 Ex ia I Ma  
Additional certifications: without  
Special features: without  
Test protocol: without test protocol  
Additional ordering information: without

Date: 23/01/2024



Specifications according to data sheet: PE 81.58