

2004 0321

Tool trolley

Code
1640755

ETIM
EC011808

EAN
4010886836507

UNSPSC
56-12-18-02

Country of origin
Germany

eCl@ss
21-07-11-00

Customs tariff number
94032080



Article description

- Body:
- Dimensions: H 812 x W 771 x D 478 mm
- Working platform in ABS, with compartments for small parts
- Storage compartment with perforated sheet (Euro perforation 10 x 38 mm), two removable drawers for small parts and door on the handle side
- Manoeuvrable and easy to steer with drive/steer handle
- Front side with Euro perforation 10 x 38 mm to fix hooks and tools
- Heel and impact protection for your safety
- Sheet steel, corrosion and scratch-resistant, powder-coated, GEDORE blue
- Drawers:
- Central locking with cylinder lock
- Wide drawers (W 480 x D 400 mm) fully extendable, removable
- Each drawer and storage compartment with safety locking, single-hand operation
- Guide rails with ball bearings
- Can be individually equipped with lengthwise and crosswise dividers (can be ordered individually)
- Load capacity per drawer 40 kg, bottom heavy-duty drawer 60 kg (not for No. 2004 1000)
- Sheet steel, corrosion and scratch-resistant, powder-coated, GEDORE blue • GEDORE high-performance chassis:
- Total load capacity 1000 kg static (750 kg dynamic)
- 2 GEDORE heavy-duty wheels with roller bearings (fixed castors, 200 mm)
- 2 GEDORE easy-running wheels with ball bearings (swivel castors, 125 mm), both with total brake each
- Even under maximum loads, the GEDORE axle design ensures: smooth running, maneuverability and directional stability
- Accessories:
- Options:
- Can be equipped with GEDORE tool modules (1500 ES/1500 CT)
- Optionally extendable with GEDORE tool chests, rear panels and tool holders
- Further drawer versions upon request
- Special colours and designs on request
- Delivery without tools and accessories

Article information

Contents (Qty of pieces)	1	Number of drawers	6
Net weight [kg]	82 kg	Load capacity per drawer [kg]	40 kg
Total length [mm]	606 mm	Drawer type	3x Type 1, H = 67 mm 2x Type 2, H = 137 mm 1x Type 3, H = 207 mm
Total width [mm]	875 mm	Fixed roller diameter (2x)	200
Total height [mm]	985 mm	Swivel castor diameter with brakes (2x)	125
Surface	powder-coated	Single pull-out stop	no
Material	sheet steel	Number of wheels	4
Colour	RAL 5017	Working height	985
Dimension (L x W x H)	985 mm x 875 mm x 606 mm	Static load carrying capacity [kg]	1000 kg
Load capacity kg	750 kg	Load capacity heavy duty drawer [kg]	60 kg
Number of crosswise dividers	2	RAL colour tone	blue
Number of lengthwise dividers	3		