

EV440 - EV4 Stretch Detachable Holster Trouser

Collection: EV4™

Range: Workwear

Shell Fabric: Titanmill Ultra Stretch: 92% Nylon, 8% Elastane

Outer Carton: 14



Product information

The EV4 Stretch Holster Trouser offers an enhanced ergonomic design, featuring laser cut ventilation for optimal airflow during work. With a high-rise back waistband and side elasticsation, it provides excellent protection in all working positions. The trousers include pre-bent, top-loading adjustable knee pad pockets, spacious front pockets, and versatile zip thigh pockets for secure storage of phones, pens, and tools. Triple stitching throughout ensures maximum durability.

EV4™

When it comes to facing tough working conditions, your workwear is your first line of defence. That's why we have developed EV4, a groundbreaking workwear collection designed to provide unparalleled protection from the harshest environments.

Workwear

Portwest workwear offers a range of designs and features suitable for many end uses. Quality fabrics and construction techniques are used guaranteeing comfort and safety. Tested to withstand the rigours of everyday wear each garment has been carefully designed and manufactured to ensure optimum quality at the best price.

Standards

EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)

Features

- Extremely water resistant PFAS free Texpel™ Splash Eco fabric finish, water beads away from fabric surface
- 4-way stretch fabric for ease of movement and added comfort
- 17 pockets for ample storage, including a rule pocket
- Zip off holster pockets for added versatility
- 2 Side pockets
- Welt pocket
- 2 back pockets with one open and one featuring a flap
- Concealed mobile phone pocket
- 1 Thigh pocket with zip closure
- 1 Rule pocket
- 1 Pen pocket

EV440 - EV4 Stretch Detachable Holster Trouser

Commodity Code: 6203431100

Test House

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
EV440BKR26	Black	60.0	40.0	23.0	0.9070	0.0552	5036108416851	15036108902634
EV440BKR28	Black	60.0	40.0	23.0	0.9990	0.0552	5036108416868	15036108902641
EV440BKR30	Black	60.0	40.0	23.0	0.9130	0.0552	5036108416875	15036108902658
EV440BKR32	Black	60.0	40.0	23.0	0.9280	0.0552	5036108416882	15036108902665
EV440BKR33	Black	60.0	40.0	23.0	0.9340	0.0552	5036108416899	15036108902672
EV440BKR34	Black	60.0	40.0	23.0	0.9430	0.0552	5036108416905	15036108902689
EV440BKR36	Black	60.0	40.0	26.0	0.9610	0.0624	5036108416912	15036108902696
EV440BKR38	Black	60.0	40.0	26.0	0.9820	0.0624	5036108416929	15036108902702
EV440BKR40	Black	60.0	40.0	26.0	1.0010	0.0624	5036108416936	15036108902719
EV440BKR41	Black	60.0	40.0	26.0	1.0240	0.0624	5036108416943	15036108902726
EV440BKR42	Black	60.0	40.0	26.0	1.0320	0.0624	5036108416950	15036108902733
EV440BKR44	Black	60.0	40.0	26.0	1.0560	0.0624	5036108416967	15036108902740
EV440BKR46	Black	60.0	40.0	26.0	1.0830	0.0624	5036108416974	15036108902757
EV440BKR48	Black	60.0	40.0	26.0	1.0920	0.0624	5036108416981	15036108902764