



Type	57903 201 111	Housing	
Designation	Mag Pro Wireless Power Bank 5.000	Material.....	Plastic
Chemical system	Lithium-Polymer	Upper casing colour.....	Black
Cell configuration.....	1x Li-Polymer Pouch (3.7V, 5000mAh, 18.5Wh)	Lower casing colour.....	Black
Cell size.....	55 mm x 65 mm		
Total cell capacity.....	5000 mAh	Dimensions	
Rated capacity.....	2960 mAh @ 5V/1A	Length.....	92.4± 1 mm
		Width.....	61.4± 1 mm
Input	10W max.	Height.....	15.3± 1 mm
USB Type C.....	5V/2A	Weight.....	135g ±3g
Output	12W max.		
USB Type C.....	5V/2.4A 9V/1.33A 12V/1A	Ambient Temperature	
Wireless Output (Qi).....	5W, 7.5W	Charging.....	0-50 °C
		Discharging.....	-10-55°C
Safety Features		Storage.....	-10°C-60°C
Short circuit protection	Input Overvoltage protection		
NTC temperature protection	UN38.3 cell conformity	Frequency band	109.6 kHz – 148.6 kHz
Overcharge protection	UL1642 cell conformity		
Deep discharge protection			
Overcurrent protection			

Indications for SoC..... 2 different LEDs behind the VARTA logo:
blue and white
<30% = white LED solid
31-70% = light blue LED solid
71-100% = dark blue LED solid

Indications for In and Out..... <30% = white LED breathing
31-70% = light blue LED breathing
71-100% = dark blue LED breathing

Power IN.....

Primary..... 5V/9V DC

Secondary..... 3.6V DC

Power OUT.....

Primary..... 3.6V DC

Secondary..... 5V/9V DC

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries