

INJECTION • INFUSION



Cannulas, Disposable

Highly transparent barrel.
Box of 100 pieces.

Articles	Size	Colour	Art.-No.
Cannula	G 20	Yellow	20 09 301
Cannula	G 21	Green	20 09 302
Cannula	G 22	Black	20 09 303
Cannula	G 23	Blue	20 09 304
Cannula	G 23	Blue	20 09 305
Cannula	G 26	Brown	20 09 306
Cannula	G 27	Grey	20 09 307



Syringes, Disposable

Secure piston stop, cylinder PP, transparent, sterile EO.

Articles	Size	Art.-No.
Syringes	2 ml	20 09 051
Syringes	5 ml	20 09 052
Syringes	10 ml	20 09 054
Syringes	20 ml	20 09 055



SAFETY Syringe and SAFETY Cannula

NEW

Two parts, retractive (mechanical withdrawal of the cannulas into the syringe), secure injection with luer-lock. Sterile.

The safety mechanism can only be activated in conjunction with the SAFETY cannula.

- SAFTEY cannula can not be used with other luer or luer-lock syringes.
- Packaging units à 100 pieces

Articles	Size	Art.-No.
SAFETY Syringe	2 ml	20 09 060
SAFETY Syringe	5 ml	20 09 061
SAFETY Syringe	10 ml	20 09 062
SAFETY Cannula	Nr. 1 G 20	20 09 520
SAFETY Cannula	Nr. 2 G 21	20 09 521
SAFETY Cannula	Nr. 14 G 23	20 09 523
SAFETY Cannula	Nr. 16 G 23	20 09 524



Cannulas, Vasofix®

Sterile. ISO Standard 10.555-1/5.

Articles	Size	Colour	Art.-No.
Cannula	0.9 x 25 mm	G 22 Blue	20 09 325
Cannula	1.1 x 33 mm	G 20 Pink	20 09 326
Cannula	1.3 x 45 mm	G 18 Green	20 09 327
Cannula	1.5 x 45 mm	G 17 White	20 09 328
Cannula	1.7 x 50 mm	G 16 Grey	20 09 329
Cannula	2.2 x 50 mm	G 14 Orange	20 09 330
Mandrine	0.9 and 0.8	G 22 Blue	20 09 370
Mandrine	1.1 and 1.0	G 20 Pink	20 09 371
Mandrine	1.3 and 1.2	G 18 Green	20 09 372
Mandrine	1.5 and 1.4	G 17 White	20 09 373
Mandrine	1.7	G 16 Grey	20 09 374
Mandrine	2.2 and 2.0	G 14 Orange	20 09 375



Safety Cannulas, Vasofix®

IV Catheter with injection port and self activating protection against needlestick injuries and related infections. ISO standard 10.555-1/5.

Articles	Size	Colour	Art.-No.
Safety Cannula	0.9 x 25 mm	G 22 Blue	20 09 450
Safety Cannula	1.1 x 33 mm	G 20 Pink	20 09 451
Safety Cannula	1.3 x 45 mm	G 18 Green	20 09 452
Safety Cannula	1.5 x 45 mm	G 17 White	20 09 453
Safety Cannula	1.7 x 50 mm	G 16 Grey	20 09 454
Safety Cannula	2.2 x 50 mm	G 14 Orange	20 09 455



Butterfly Cannulas, Venofix-A

With flexible wings. 30 cm PU-tube, pressure free installation, sterile.

Articles	Size	Colour	Art.-No.
Butterfly Cannula	0,50 x 15 mm	G 25 Orange	20 09 334
Butterfly Cannula	0,65 x 20 mm	G 23 Blue	20 09 335
Butterfly Cannula	0,80 x 20 mm	G 21 Green	20 09 336
Butterfly Cannula	1,10 x 20 mm	G 19 Beige	20 09 337

DIAGNOSTIC