



Sounds like productivity



2-port or 6-port dock charger included

PX650

PMR446 Business Two-Way Radios



Professional & discreet design

Designed for business use with a sleek, durable, and easy-to-operate form factor



Splashproof (IP54) rating

Water resistant rating for weather exposure or unpredictable environments



Ultra-long runtime

All-day usage up to 18 hours (90% Standby / 5% Talk / 5% Listen)



16 Channels

Securely communicate across 16 channels with 121 privacy codes



Swivel holster

Position your radio at any angle for optimal comfort



Voice-activated transmission (VOX)

Hands-free usage to automatically transmit when you speak

EMERGENCY ALERT

Dedicated button for time-sensitive or emergency situations

ERGONOMIC CONTROLS

Large, tactile dedicated volume and channel knobs for one-handed operation

2.5 MM HEADSET JACK

Choose from a range of accessories, including speaker mic and headset functionality

USB-C JACK

For charging without a dock



DOCK CHARGER

Includes a 2-dock or 6-dock charger



180° SWIVEL HOLSTER

For easy access on the job

LITHIUM-ION BATTERY

Up to 18 hours of battery life keeps you connected for your entire workday

Part#	Two-Way Radio Description	QTY
0190003-1	Pro Business PMR446 two-way radio, includes 2-dock charger	2 pk
0190003-2	Pro Business PMR446 two-way radio, includes 6-dock charger	6 pk

Part#	Accessory Headsets Description	QTY
GA-SV01	Surveillance style headset with microphone	1
GA-SV01 2P	Surveillance style headset with microphone	2 pk
0010120-1	D-Style headset	1
0010121-1	C-Style around the ear headset	1
0010122-1	C-Style in ear headset	1
0010123-1	C-Style in ear headset with foam earpiece	1