

# Rittal – The System.

Faster – better – everywhere.

## ▶ **Socket strip with power measurement – DK 7240.301**

Date : Apr 26, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Socket strip with power measurement – DK 7240.301

created: 26.04.2021 build on www.rittal.com/uk-en



## Product description

<b>Description:</b>	The socket strip 7x CEE 7/3 (type F - earthing-pin socket) with integrated display measures the power consumed by the connected equipment. The 482.6 mm (19") long socket strip may optionally be mounted on the 482.6 mm (19") mounting frame, on the enclosure frame or in the rear section of wall-mounted distributors. The installation bracket may be mounted in four different positions for variable mounting. Without additional mounting accessories, the socket strip may be inserted into all sections with a 25 mm hole pattern.
<b>Benefits:</b>	Measurement accuracy of $\pm 5\%$
<b>Function principle:</b>	Measurement of current, voltage, frequency, active power, active energy and phase shift
<b>Material:</b>	Aluminium section, natural anodised Socket inserts: Polycarbonate
<b>Supply includes:</b>	Socket strip 2 mounting brackets Assembly parts Operating manual With 3 m connection cable (wire end ferrules)

## Product description

<b>Design:</b>	Mit Display
<b>Dimensions:</b>	Width: 19" Height: 45 mm Depth: 50 mm Length: 482.6 mm
<b>Installation options:</b>	Components with a 25 mm pitch pattern 482.6 mm (19") level

Enclosure frame  
IT wall-mounted distributor, at the rear, horizontal (adequate width provided)

<b>Mounting dimensions:</b>	464.1 mm
<b>Operating temperature:</b>	Operation (environment): +5 °C...+45 °C Bearing: -15 °C...+60 °C
<b>Ambient humidity (non-condensing):</b>	Bearing: 10 % - 80 %
<b>Rated voltage:</b>	230 V AC
<b>Rated current (max.):</b>	16 A
<b>Equipment (electrical):</b>	Number of sockets: 7 Jack/socket (type): D, earthing-pin (type F, CEE 7/3) Colour of socket: RAL 7035 Length of connection cable: 3 m
<b>Connection cable (type):</b>	H05VV-F3G1.5 with wire end ferrules
<b>Packs of:</b>	1 pc(s).
<b>Weight/pack:</b>	1.08 kg
<b>Copper weight (kg per piece):</b>	0
<b>EAN:</b>	4028177709416
<b>Customs tariff number:</b>	85369095
<b>ETIM 7.0:</b>	EC000330
<b>ETIM 6.0:</b>	EC000330
<b>eCl@ss 8.0/8.1:</b>	27142604
<b>eCl@ss 6.0/6.1:</b>	27142604
<b>Product description:</b>	DK Socket strip, CEE 7/3 (type F), 7-way, 230 V (AC), 16 A, LHD: 482,6x45x50 mm, with display
<b>Approvals</b>	
<b>Certificates:</b>	EAC
<b>Declarations:</b>	Declaration of conformity

