

FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and durability.
- **Flanged Design:** Offers easy installation and secure positioning.
- **Dynamic Load Rating of 14 N/mm²:** Ensures reliable performance under varying loads.
- **Static Load Rating of 50 N/mm²:** Supports high load capacity for demanding applications.
- **Outside Diameter of 1.12 in:** Fits standard housings for seamless integration.

RS PRO 0.87 in Flanged Plain Bearing

RS Stock No: 528-872



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 0.87 in Flanged Plain Bearing is designed for applications requiring reliable rotational movement with minimal friction. Ideal for use in machinery and equipment, this bearing ensures smooth operation and longevity, making it a cost-effective solution for industrial needs.

General Specifications

Bore Size	0.87 in
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	1.12 in
Width	1-1/4 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

