



mecalectro

Industrial Solenoid – 8.13.AB.83



Stroke: 14 mm

Force at beginning of stroke (FM: 100/25/5%):
2/10/29 N

Force at end of stroke (FM: 100/25/5%):
4/18/50 N

Power Consumption (FM: 100/25/5%):
12/40/200 W

Total mass: 300 g

Degree of protection / Energetic class: IP 40 / B

Standard supplies: 24Vcc

Possibles supplies: From 12 to 220Vcc

Duty Cycle: Permanent, impulsions (100 / 40 / 25 / 15 / 5 %)

Standard: NF C 79300

Examples of applications: Automation, blocking, composting, distribution, stamping, punching.