

Datasheet

Stock No: 775-6075

# RS Pro 3 Core Black 2183Y Mains Power Cable



## Features:

Used on household appliances in covered, dry, steamed and humid areas, where low mechanical stress exist. Flexible wires with fine stranded copper conductors, PVC insulation, PVC sheath.

## Specifications:

Max. Operating temperature: 70c

Short circuit temperature: 160c (man. 5 sn.)

Rated Voltage: 3300/300V

## Dimensions, Weights and Electrical Properties:

Nominal cross-section	Diameter (approx)	Weight (approx)	Resistance at 20c	In Air at 30c
mm <sup>2</sup>	mm	Kg/km	Ohm/km	A
3x0,50	5,39	40,62	39	3