

Rittal – The System.

Faster – better – everywhere.

Interlock kits for VX – VX 8951.000

Date : Jun 18, 2019

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Interlock kits for VX – VX 8951.000

created: 18.06.2019 on www.rittal.com/com-en



Product description

Description: Including main door latch for safety locking of enclosures and bayed enclosure suites in accordance with UL regulations. Tested in conjunction with actuator lever for master switch.

Benefits: Meets the requirements of UL 508 A
In conjunction with the operating mechanism, adjacent door lock and interconnecting rods, these requirements are also met for bayed combinations
May be mounted optionally on the left or right of the enclosure. With this cover, all single-door bayed enclosures may be configured as isolator door enclosures. The complete installation surface of the enclosure is retained.
In conjunction with the mounting plate infill, the mounting surface of the main enclosure can be enlarged by up to 14%.
Two cut-outs for actuator levers on the front, for internal mounting at varying heights

Applications: Allen Bradley: 1494 F-M1/P1/S1 and 140 U-K-FCX04
Square D: 9422 A1
General Electric: TDA Type 1 and 2
Eaton NZM2(3)-XSH-12-...-NA for type 4x
Eaton NZM2(3)-XSH-12-...-NA for type 12
Siemens: Operating mechanism with bowden cable – complete kits
3VA9137-0CK12 for 3VA51 up to 125 A; plastic actuator; NEMA 1, 12, 3R; black=OFF, red=ON
3VA9137-0CK12 for 3VA51 up to 125 A; epoxy-coated steel actuator; NEMA 1, 12, 3R; black=OFF, red=ON
3VA9277-0CK12 for 3VA52/62 up to 250 A; plastic actuator; NEMA 1, 12, 3R; black=OFF, red=ON
3VA9277-0CK12 for 3VA52/62 up to 250 A; epoxy-coated steel actuator; NEMA 1, 12, 3R; black=OFF, red=ON
3VA9477-0CK12 for 3VA53/54/63/64 up to 600 A; plastic actuator; NEMA 1, 12, 3R; black=OFF, red=ON
3VA9477-0CK12 for 3VA53/54/63/64 up to 600 A; epoxy-coated steel actuator; NEMA 1, 12, 3R; black=OFF, red=ON

Material: Sheet steel, 1.5 mm

Surface finish: Powder-coated

Colour:	RAL 7035
Protection category IP to IEC 60 529:	IP 55
Protection category NEMA:	NEMA 12
Supply includes:	Main door lock, cover plate and assembly parts.
Note:	Cover may only be mounted on a single-door enclosure with tubular door frame

Product features

Dimensions:	Width: 125 mm Height: 2000 mm Depth: 500 mm
Packs of:	1 pc(s).
Weight/pack:	19 kg
Copper weight (kg per piece):	0
EAN:	4028177921061
Customs tariff number:	94039010
ETIM 6.0:	EC000261
ETIM 5.0:	EC000261
eCl@ss 8.0/8.1:	27180101
eCl@ss 7.0/7.1:	27189290
eCl@ss 6.0/6.1:	27189290
eCl@ss 5.1/5.1.4:	27182101
Product description:	VX Isolator door cover, WHdepth 125x2000x500 mm

Approvals

Approvals:	UL + C-UL
-------------------	-----------