

245611**Manual bending tool set**

hydraulic, heavy duty, 11 pieces

Code	ETIM
1585495	EC011119
EAN	UNSPSC
4017981245623	27-11-25-01
Country of origin	eCl@ss
Italy	21-04-16-03
Customs tariff number	
84622900	

**Article description**

- Dimensions from 6 to 22 mm Ø to 90°
- For soft copper pipes EN 1057 up to 22 mm (also heat-insulated), multi-layer composite pipes up to 20 mm, precision steel pipes EN 10305-3 (DIN 2394) up to 18 x 2 mm and annealed stainless steel pipes up to 18 x 1.2 mm
- With 10 bending moulds for tubes with Ø 6, 8, 10, 12, 14, 15, 16, 18, 20 and 22 mm and corresponding counter holders
- Hydraulic drive without great effort
- In plastic box No. 245690

Article parts list

1 base unit, hydraulic No. 245670, 10 bending tools, for pipes with Ø 6, 8, 10, 12, 14, 15, 16, 18, 20, 22 mm, 1 plastic case No. 245690

Article information

Contents [Qty of pieces]

11

Net weight [kg]

7,5 kg