



Multi Purpose



Light Duty

Increased visibility multipurpose gloves, ensuring hand protection in dark environments

- **Heightened protection:** Thanks to their extra visibility palm and back-of-hand, ActivArm® 97-012 industrial gloves improve worker safety in low-light conditions, protecting hands while ensuring a firm grip on wet and dry surfaces
- **Improved comfort:** These nitrile-coated work gloves feature a 15-gauge liner that guarantees comfortable all-day wear, keeping hands dry and affording ample dexterity for handling smaller items
- **Advanced ergonomics:** ActivArm® 97-012 protective gloves are naturally curved, resulting in a relaxed fit and reduced tension
- **Reduced surface defect risks:** Silicone-free, these work gloves prevent potential surface defects while ensuring a high-quality finish



Industries

- Mining
- Chemical

Applications

- Signalling/Positioning
- Positioning
- Operating of heavy machinery
- Loading and hauling
- Hydraulic repair
- Product inspection
- Shipping and loading of product
- Vehicle Maintenance
- Conveyer and longwall maintenance
- Loading trucks & vehicles
- Product shipping, transport and delivery
- Lock smith

Key Features

- **Extra visibility back and palm:** For hand protection in darker areas
- **15-gauge liner:** Breathable tactility and all-day comfort assured
- **Ergonomic design:** For fitted safety gloves with minimal hand fatigue

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



3131A

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® 97-012	Finishing: Palm Coated Coating Material: Nitrile Liner Material: Nylon, Spandex Cuff Style: Knitwrist	15	7, 8, 9, 10, 11	215-272 mm/ 8.5-10.7 inches	Orange	12 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.