



Main

Range	OptiLine
Product name	OptiLine 45
Cabling installation system	Pole
Product type	Pole
Device presentation	Empty
Type of pole	Two-sided
Pole/post surface finish	Anodized
Pole fixing mode	Tension-mounted
Socket additional information	Unearthed

Complementary

Additional information	Adjustability of ceiling fixing 400 mm
Colour	Natural
Front opening size	45 mm
Material	Aluminium anodized
Quantity package 1 / unit	Set of 1
Height	3900...4300 mm
Depth	90 mm
Width	116 mm

Environment

Operating temperature	-25...60 °C
IP degree of protection	IP30

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations