




Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #2018849-1
ASSY, SEATING TL, 6 ROW, 6 COL

TE Part #1-5084615-0
0.8FH,P06H.5,200,30/Sn,TU

TE Part #5787885-1
200 CMP DCK RA PLG INV SHL 3.4

TE Part #5176374-2
AMP FH CONN REC V 60P (H=14)

TE Part #5084615-2
0.8FH,P06H.5,060,30/Sn,TU

TE Part #2170262-2
SFP+ 1X1 HEAT SINK, SPECIAL TYPE

TE Part #205736-4
15 RCPT SP/MS STD

TE Part #7-1542006-8
HTS804-U=29MM HS ASSY ULTEM CL

TE Part #2149977-2
IMP100S,H,V4P6C,UG,REW39,4.9

TE Part #2007821-2
IMP100S,H,V4P10C,UG,LEW39,4.9

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_120953-7_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_120953-7_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_120953-7_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

POWER_CONNECTORS_CATALOG_SEC01_BOARD_TO_BOARD

English

2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1

English



Product Specifications

English

Agency Approvals

UL Report

English