

## ITX 19 L T30-100

### Screwdriver bit socket 1/2"

for recessed TX head screws

Code	ETIM
<b>6152500</b>	<b>EC002213</b>
EAN	UNSPSC
<b>4010886615256</b>	<b>27-11-17-01</b>
Country of origin	eCl@ss
<b>Germany</b>	<b>21-04-04-02</b>
Customs tariff number	
<b>82079030</b>	



### Article description

- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- Chromed
- With pressed-in pin in GEDORE vanadium special steel, gun-metal finish

### Article information

Contents (Qty of pieces)	1	Standard	DIN 3120 - C 12,5 ISO 1174
Net weight [kg]	0,096 kg	Backup	Ball Catching Cricket
Total length [mm]	100 mm	Tip size TX (recess)	T30
Total width [mm]	22,5 mm	Screw size	M6 - M7
Surface	chrome-plated	Tip size TX (recess) [mm]	5,52 mm
Material	Chrome-vanadium steel	Tip length	62,0 mm
Drive connector square female (metric)	12,5 mm	Insert Ø Actuator	22,5 mm
Drive connector square female [inch]	1/2"		