

7 10

Combination spanner with same size each end

metric

Code	ETIM
6090050	EC002176
EAN	UNSPSC
4010886609002	27-11-17-13
Country of origin	eCl@ss
Germany	21-04-01-05
Customs tariff number	
82041100	



Article description

- Acc. to DIN 3113, Form A, ISO 3318, ISO 7738
- Chrome-vanadium steel 31CrV3, chrome-plated
- Carefully forged and professionally machined
- Slim jaw and jaw walls make this spanner lighter overall
- Jaw: ground precisely to exact nominal size for optimum contact areas
- Ring: 15° offset from shaft, with UD profile for gentle transmission of force
- Overloading indicated by deformation
- Secure grip thanks to hollow shaft - very ergonomic and handy
- Glare-free look due to matt chrome
- Designed for universal use
- Top-grade industrial quality for the hardest of continuous use
- Size 3 to 5.5 with hexagonal ring, from 6mm with UD profile
- * not standardised

Article information

Contents [Qty of pieces]	1	Width of head 2 [mm]	23 mm
Net weight [kg]	0,033 kg	Head height 2 [mm]	4,2 mm
Total length [mm]	140 mm	Head height 1 [mm]	7 mm
Total width [mm]	23 mm	Width of head 1 [mm]	15,5 mm
Total height [mm]	10 mm	Mouth position 1	15°
Surface	chrome-plated	Ring profile	UNIT-DRIVE
Material	31CrV3	Weight	0,070 lbs
Standard	DIN 3113 - Form A ISO 3318 ISO 7738	Ring angle	15°
Width across flats 1 [mm]	10		