

# Coupling connectors

Sicma

## 24 way sealed coupling housings for 1.5 + 2.8 mm terminals

### Features

- High density connector system using 6 x [2.8 mm] and 18 x [1.5 mm] terminals
- 3 rows 5 x 5 mm pitch
- Circumferential interface seal on female housing
- Rear sealing by a pre-mounted mat-seal
- Pre-assembled front grids support blade terminal guiding and mating
- Terminal position assurance (T.P.A.)
- Easy locking cam
- Mechanical polarization
- Several colour codings available
- 2 locking cam positions possible



### Performance characteristics

- Temperature range: from -40°C to +125°C
- Contact retention force: > 65 N for 1.5 mm terminals > 80 N for 2.8 mm terminals
- Contact insertion force: < 12 N for 1.5 mm terminals < 15 N for 2.8 mm terminals
- Connector mating force: < 70 N
- Sealing protection: IP 68
- Acceptable wire range: from 0.35 mm<sup>2</sup> to 4 mm<sup>2</sup>

### Construction

- Housing material: PBT
- Interfacial seal: Silicone
- Grommet seal: Silicone

### Tooling

- T.P.A. removal tool: 210S040
- Terminal removal tool
  - Female terminal: 210S048
  - Male terminal: 210S049

### Connector compatibility

- Usable terminals:
  - Sicma-2 1.5 mm female terminals
  - Sicma-2 1.5 mm male terminals
  - Sicma-2 2.8 mm female terminals
  - Sicma-2 2.8 mm male terminals
  - Sicma-3 1.5 mm female terminals
  - Sicma-3 1.5 mm male terminals
  - Sicma-3 2.8 mm female terminals
  - Sicma-3 2.8 mm male terminals
- Other applications: see chapter 5 and 7

Part Numbers	No. of position	Terminal size	Type	Colour
211 PC249S0005	24	18 x [1.5 mm] + 6 x [2.8 mm]	Female housing	Black
211 PC249S1005	24	18 x [1.5 mm] + 6 x [2.8 mm]	Female housing	Brown
211 PC249S8005	24	18 x [1.5 mm] + 6 x [2.8 mm]	Female housing	Grey
211 PC249S6005	24	18 x [1.5 mm] + 6 x [2.8 mm]	Female housing	Blue
211 PL249S0005	24	18 x [1.5 mm] + 6 x [2.8 mm]	Male housing	Black
211 PL249S1005	24	18 x [1.5 mm] + 6 x [2.8 mm]	Male housing	Brown
211 PL249S8005	24	18 x [1.5 mm] + 6 x [2.8 mm]	Male housing	Grey
211 PL249S6005	24	18 x [1.5 mm] + 6 x [2.8 mm]	Male housing	Blue
211 A 247 001			Locking cam	Purple

# Coupling connectors

Sicma

## 24 way sealed coupling housings for 1.5 + 2.8 mm terminals

### Dimensional characteristics

