

SEK CAB FLAT SH RND AWG28/7 64P 100m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 064 7010
Specification	SEK CAB FLAT SH RND AWG28/7 64P 100m
HARTING eCatalogue	https://harting.com/09180647010

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)

Version

Cable length	100 m
Number of cores	64
Core structure	AWG 28/7
Shielding	Shielded

Technical characteristics

Impedance	100 Ω
Limiting temperature	-30 ... +75 °C unmoved -20 ... +75 °C moved
Conductor resistance @ 20 °C	$\leq 216 \Omega/\text{km}$

Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	UL 1581
	UL PLCC, CL2
Approvals	CE

Commercial data

Packaging size	1
Net weight	23,700 g
Net weight	220 g/m
Country of origin	USA
European customs tariff number	85444993
GTIN	5713140273856
eCl@ss	27061801 Data and communication cable (copper)
ETIM	EC003249
UNSPSC 24.0	26121609