

Item code

# TAPH 24.32



## Brief description:

surface mounting housings with 2 levers, size "104.27" , M32, HYGENIC enclosures T-TYPE /H version, IP66 and IP69

Product description	
Version	HYGENIC enclosures T-TYPE /H version
Series	Surface mounting housings with 2 levers
Product type	with two levers in thermoplastic material
Family	T-TYPE insulating enclosures
Size	size "104.27"
Technical data	
Operating temperature range (min, max)	-40°C ... +70°C
Material	thermoplastic
IP degree of protection	IP66/IP69
Cable entry	M32
Other technical details	
Weight	235,00 g

Approvals / Standards	
Quality mark	 (type:12), EAC
Conformity	CQC, CE
General ordering information	
EAN code	8015747209960
Tariff number	85369095
Packaging Information	
Packaging length	330,00 mm
Packaging height	220,00 mm
Packaging width	310,00 mm
Packaging weight	4,70 kg
Packaging volume	22,51 dm <sup>3</sup>
Packaging description	Carton box
Packaging quantity	20 Pcs
Packaging EAN code	8015747210133
Sub-packaging weight	1,18 kg
Sub-packaging description	Plastic pakaging
Sub-packaging quantity	5 Pcs
Sub-packaging EAN barcode	8015747210140