

5958U

Assortment of 85 tools

Universal use

		art.
	059581008	5958U

- n. 17 **42:** combination wrenches 6÷22 mm
- n. 12 **96N/SC12:** offset hexagon key wrenches Ø 2÷10 mm
- n. 13 **920A/SB13:** 1/2" square drive hexagon sockets with rail Ø 10÷22 mm
- n. 8 **920A/SB8:** 1/2" square drive hexagon sockets with rail Ø 23÷32 mm
- n. 1 **920/21:** 1/2" drive extension bar 125 mm
- n. 1 **920/22:** 1/2" drive extension bar 255 mm
- n. 1 **920/25:** 1/2" drive universal joint
- n. 1 **920/42:** 1/2" drive sliding T-handle
- n. 1 **920/55:** 1/2" reversible ratchet ⌚
- n. 1 **1032:** circlip pliers straight, internal ⌚ 180 mm
- n. 1 **1036:** circlip pliers straight, external ⌚ 175 mm
- n. 1 **1048N:** slip joint pliers, slip-proof PVC coated handles 250 mm
- n. 1 **1052:** self - locking pliers 240 mm
- n. 1 **1084BM:** Heavy-duty diagonal cutting nippers ⌚ 160 mm
- n. 1 **1128BMX:** electrician's scissors, straight blades 147 mm
- n. 1 **1150BM:** combination pliers bright chrome-plated, bi-material handles ⌚ 180 mm
- n. 1 **1166BM:** Extra-long needle nose pliers ⌚ 160 mm
- n. 7 **1260:** screwdrivers for slotted head screws ⌚ 3x75 - 3,5x100 - 4x125
5,5x150 - 6,5x150 - 8x200 - 10x200 mm
- n. 4 **1262/S4:** screwdrivers for cross head Phillips® screws ⌚ PH0x60 - PH1x80
PH2x100 - PH3x150 mm
- n. 1 **1370:** engineer's hammer 300 g
- n. 1 **1390:** soft face hammer Ø 35 mm
- n. 1 **1692:** measuring tape 5 m
- n. 5 **1719BMA...S5:** Set of 5 second-cut files, with handles 200 mm
- n. 1 **1725:** hacksaw frame, aluminium handle
- n. 1 **1754:** plastic oil can 150 cc
- n. 1 **1771:** snap - off blade utility knife 170 mm

