



Main

Range	Resi9
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Lines description	3L
Length in 18 mm modules	12

Complementary

Number of ways	4 ways 3 L
Poles configuration for 1 way	1 x 3P
Connection pitch	18 mm
Connector type	Fork
Distance between way	54 mm
Marking	L1 L2 L3
Insulation	Insulated
Device presentation	Cuttable
[Ie] rated operational current	63 A at 40 °C
[Ue] rated operational voltage	400 V AC Ph/Ph
[Ui] rated insulation voltage	500 V AC
Mounting mode	Horizontal
Mounting location	Bottom on biconnect
9 mm pitches	24
Width	220 mm
Colour	White (RAL 9003)
Range compatibility	Acti 9 K60 Resi9 MCB Resi9 RCBO Resi9 RCCB Resi9 SWITCH

Environment






Standards	IEC 60947-7-1 IEC 61439-2
Product certifications	CE
Fire resistance	960 °C (30 s) conforming to IEC 60695-2-1
Pollution degree	3

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	82 g
Package 1 Height	2.8 cm
Package 1 width	21.7 cm

Package 1 Length	1.7 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	480 g
Package 2 Height	5.6 cm
Package 2 width	25 cm
Package 2 Length	8.8 cm
Unit Type of Package 3	S04
Number of Units in Package 3	195
Package 3 Weight	19.865 kg
Package 3 Height	30 cm
Package 3 width	40 cm
Package 3 Length	60 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------