
Features

- For SF24 Cable Mount Connectors
- IP67 (when mated)
- SF24 Series
- Push-Pull Coupling
- Used in Factory Automation, Robotics, Industrial Machinery, Railway & Transportation, Aerospace & Defence, Medical Equipment, Renewable Energy Systems etc.

RS PRO Circular Connector Dust Caps

RS Stock No.: 868159



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

The RS Pro SF24 Series offers a range of high-precision, waterproof connectors designed to meet IP67 sealing standards. Featuring a push-pull coupling mechanism, these connectors ensure fast, secure, and reliable mating. The chrome-plated brass housings provide excellent durability while maintaining a sleek, professional appearance.

Available in in-line cable-to-cable and cable-to-panel configurations, the series includes plugs and receptacles with either male pins or female sockets. Suitable for both data and power transmission, the RS Pro SF24 Series is ideal for use in medical, communications, and test & measurement applications.

General Specifications

Shell Material	Brass with chrome plating
Mating Type	Push-Pull
Mating Cycles	500
Colour	Silver

Mechanical Specifications

Connector Series	SF24

Operation Environment Specifications


Operating Temperature	-40^{0}C to 85^{0}C

Protection Category

IP Rating	IP67 (when mated)

Approvals

Compliance/Certifications	RoHS, CE



Mating Parts

Cable Mount Connectors	868071 868072 868073 868074 868102 868103 868104 868105 868106 868107 868108 868109 868110 868111 868112 868113 868114 868115 868116 868117 868118 868119