



## Main

|                             |   |
|-----------------------------|---|
| Range                       | Spacial   |
| Product name                | Spacial CRN                                       |
| Application                 | Multi-purpose                                     |
| Category                    | Compact enclosure                                 |
| Enclosure nominal height    | 800 mm  |
| Enclosure nominal width     | 600 mm  |
| Enclosure nominal depth     | 200 mm  |
| Installation accessory type | Wall-mounting                                     |
| Device composition          | 1 body<br>1 cable gland plate<br>1 door<br>1 lock |
| Door type                   | Plain   |
| Mounting plate description  | Without mounting plate                            |

## Complementary

|                             |  |
|-----------------------------|--|
| Body type                   | Back welded with double profile forming a protected sealed area<br>Sides made from a single folded section |
| Number of doors             | Front face: 1 door(s)  |
| Door opening side           | Reversible (120 °)   |
| Lock type                   | 3 mm double-bar lock   |
| Type of gland plate         | Standard   |
| Accessibility for operation | Front  |
| Removable parts             | Door by hinges<br>Cable gland plate by screws  |
| Material                    | Body: steel  |
| Surface finish              | Epoxy-polyester powder   |
| Colour                      | Grey (RAL 7035)  |

|                        |                     |
|------------------------|---------------------|
| Standards              | IEC 62208           |
| Product certifications | CUL<br>UL<br>DNV-GL |
| Net weight             | 18.138 kg           |

## Environment

|                         |                              |
|-------------------------|------------------------------|
| IP degree of protection | IP66 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Weight             | 18.344 kg |
| Package 1 Height             | 21.5 cm   |
| Package 1 width              | 61.5 cm   |
| Package 1 Length             | 81.5 cm   |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|