
Product Information

INKJET PRINTERS

Stylus PHOTO RX500

SPECIFICATION

Part number: C11C544011CU

PRINT FUNCTION

Print Technology	6-colour inkjet photo printer EPSON Micro Piezo™ EPSON Variable-sized Droplet Technology with Ultra Micro Dot™ for 3pl droplets Print Head of 540 nozzles (90 nozzles per Black, Cyan, Magenta, Light Cyan, Light Magenta, Yellow)
Print Quality	Up to 5760* x 1440dpi *optimised dpi on suitable media using RPM (Resolution Performance Management)
Print Speed	Black Text (Economy Mode) 17 ppm Colour Text (Economy Mode) 16 ppm Photo Bike Image 10 x 15cm (Photo Mode) 54 seconds Photo Bike Image A4 (Photo Mode) 120 seconds
Paper Handling	A4, 9 x 13cm, 10 x 15cm, 13 x 18cm, 20 x 30cm, 3.5 x 5", 4 x 6", 5 x 8", 8 x 10", A5, A6, B5, Legal, Executive, Letter, Half Letter, EPSON Panoramic 210 x 594mm, Envelope C6 (162 x 114mm), Envelope No 10 (241.3 x 104.8mm), Envelope DL (220 x 110mm), Envelope 220 x 132mm
Paper Weight	From 64 to 90 g/m2. Up to 255 gr/m ² using EPSON genuine media only

COPY FUNCTION

Copy Speed	Approx. 10cpm - A4 black text document (Economy mode) Approx. 8cpm - A4 colour text document (Economy Mode)
Standalone Copier Usability	LCD Control Panel, Zoom (25% - 400%), Standard, BorderFree, Small Margins, Repeat-AUTO, Repeat-4, Repeat-9, Repeat-16, Poster-4, Poster-9, Poster-16, 2-up, 4-up, Mirror

SCAN FUNCTION

Scan Technology	Flatbed, alternative 6 lines colour CCD
Colour Depth	Input 48bits/pixel, Output 48bits/pixel
Optical Density	3.3 Dmax
Scan Quality	2400 x 4800dpi Optical Resolution
Scanning Speed (600dpi)	Monochrome: 4.8msec/Line Colour: 4.8msec/Line
Scanning area (max)	261 x 297mm
EPSON Smart Panel features	Scan to E-mail, Scan to Fax, Scan to PDF, Scan to PDA, Scan to OCR, Scan and print photos, Scan and copy documents, Scan to application, Scan to Web
Transparency Unit Supported Sizes	Strip film: Maximum 6 x 35mm frames, Mount film: Maximum 4 x 35mm frames

OTHER SPECIFICATIONS

Operating System Compatibility	Windows® 98, Windows® Me, Windows® 2000, Windows® XP, Macintosh® Colour Matching, EPSON Colour management system included in Windows® and Mac drivers Windows® 98/Me/2000/XP ICM, sRGB (Windows® 98/Me/2000/XP), Apple ColorSync 2.0 compatible
Interface	USB 2.0 Hi-Speed Interface for PC and Mac connections
Dimensions	Standard (wxdxh) 456 x 439 x 256mm Operational (wxdxh) 456 x 439 x 299mm
Weight	10.0Kg
Noise Level	45dB(A) (ISO 7779)
Power Consumption	21Watts (per ISO 10561 Letter pattern - standalone copying)
Ink Cartridges	Black T0481 Capacity 630 A4 pages (ISO/IEC10561 Letter Pattern at 360dpi, 3.5% duty) and 450 A4 pages (at 360dpi, 5% duty) Colour T0482 (Cyan), T0483 (Magenta), T0484 (Yellow), T0485 (Light Cyan), T0486 (Light Magenta) Capacity 430 A4 pages (at 360dpi, 5% duty per colour)
Memory Card Connectivity	CompactFlash® (I&II), xD-Picture Card™, SmartMedia™, SD Memory Card, MultiMediaCard, Magic Gate Memory stick, Memory Stick®, Memory Stick PRO™, Memory Stick Duo and IBM Microdrive™. Adapter required for Mini SD Card and RS-MMC.

SYSTEM REQUIREMENTS

Recommended	Windows® 98, Pentium 300MHz CPU, 256MB RAM, 800MB HDD Space Windows® Me, Pentium 300MHz CPU, 256MB RAM, 800MB HDD Space Windows® 2000, Pentium 300MHz CPU, 256MB RAM, 850MB HDD Space Windows® XP, Pentium 300MHz CPU, 256MB RAM, 850MB HDD Space Mac OS 8.6 - 9.2 64MB RAM, 50MB HDD Space MacOSX PowerPC 128MB RAM, 50MB HDD Space
--------------------	---

Warranty:	1 year repair or replace Optional extension to 3 year warranty
------------------	---
