



## Main

Range of product	Canalis
Range compatibility	Canalis KT busbar trunking Canalis KH busbar trunking
Product or component type	Tap-off unit
Busbar trunking compatibility	Canalis KT busbar trunking with KH type plug-in Canalis KHF and KGF busbar trunkingplug-in
[Ie] rated operational current	250 A
Protection type	Circuit breaker: NSX250
Provided equipment	Circuit-breaker to be ordered separately
Mounting mode	Plug-in with auto-clamping system
Tap-off unit polarity	3L+N+PE

## Complementary

Device application	Medium power distribution
[Ue] rated operational voltage	690 V
[Uimp] rated impulse withstand voltage	8 kV
[Ui] rated insulation voltage	800 V
Network frequency	50/60 Hz
Control type	Extended rotary handle
Electrical connection	Cable clamp terminal 150 mm² (x1)
Door/cover opening side	Down
Standards	IEC 61439-1 IEC 61439-6
Colour	White (RAL 9001)
Width	590 mm
Depth	212 mm
Depth (door open)	520 mm
Height	371 mm
Net weight	32 kg

## Environment

Earthing system	IT TN-S TT
IP degree of protection	IP31 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
Sustainable packaging	Yes

RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins