

FEATURES

- **Sintered Bronze Material:** Provides high strength and excellent wear resistance.
- **Flanged Design:** Ensures easy installation and secure fitment.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling higher static loads effectively.
- **ISO 2795 and ISO 9001:2008 Certified:** Meets international quality and performance standards.

RS PRO 22.02 mm Flanged Plain Bearing

RS Stock No: 529-060



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable rotational movement with minimal friction. Made from sintered bronze, it offers excellent durability and performance in various industrial settings. The bearing's flanged design ensures easy installation and secure positioning, making it ideal for supporting shafts and reducing wear.

General Specifications

Bore Size	22.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	28.05 mm
Width	20 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

