







PCB LAYOUT (CONNECTOR REAR VIEW)

- RJ45 CONTACTS
- RJ45 SHELL GROUND CONTACT
- SHIELD BOX LEGS
- CONNECTOR LOCATION PINS





PANEL CUT OUT

RJXS8FP25VE

SERIES PREFIX
CONTACT LAYOUT (RJ45 STYLE)

GENDER
THERMOPLASTIC 3.8mm to 5.0mm WITH CAP
TRANSMISSION CLASS (CAT5e)
VERTICAL MOUNT (PCB THRU HOLE)
WITH EMI/RFI SHIELD



RECOMMEND MINIMUM MOUNTING PITCH



UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE:		THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER				Amphenol Amphenol Australia Pty.Ltd, 22 Industry Blvd Carrum Downs, VIC 3201			
LINEAR	ANGULAR	MATERIAL: SEE COMPONENTS	DRN:	J.W	DATE:	30/12/2024	TITLE: XLrnet, VERT, IP65, SHIELDED, W/CAP, PANEL THICKNESS 3.8-5.0	PART NO: RJXS8FP25VE	REV 1
X.X ±10	X" ±1		CKD:	P.M.	DATE:	30/12/2024			
X.X ±5	X"X' ±30'		APPD:	P.M.	DATE:	30/12/2024			
X.XX ±1	X"XX" ±15'		DO NOT SCALE	SCALE:	NTS	SIZE:			
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS		FINISH: SEE COMPONENTS		THIRD ANGLE PROJECTION		DRAWING NO. 55011544-300-1		SHEET 2/2	
DIMENSIONS IN MILLIMETRES									